

Art.-Nr.: 10.01.27.01971



VAGG 40 AC3 80 MD


The vacuum unit VAGG is supplied as a product ready to connect.

Available spare parts: vacuum gauge, oil, spare parts set float, wear parts set vacuum pump, vacuum pump

Available accessories: vacuum hose

Technical data

Attribute	Value
Suction rate (max.)	40.000 m ³ /h
Reservoir volume	80.0 l



Design data VAGG 40 AC3 80 MD

Design data

Attribute	Value
Length L	994.00 mm
Width B	435.00 mm
Height H	926.00 mm
Outside diameter D1	14.0 mm
Outside diameter D2	7.2 mm
Outside diameter D	25.00 mm

Art.-Nr.: 10.01.27.01971

**Technical data**

Attribute	Value
Max. vacuum	930 mbar
Suction rate (max.)	40.000 m³/h
Function	manual drain
Current type	Three phase A.C.

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.27.01971**Ordering Data Accessories 10.01.27.01971**

Typ	Artikelnummer
Vacuum distributor	VTR-ZF 8x 1TN MAN/KVZ 10.01.27.00126

**Ordering Data Spare Parts 10.01.27.01971**

Typ	Artikelnummer
Spare part	ERS VAGG 6-63 10.01.27.01456
Vacuum pump	EVE-OG 40 AC3 10.03.02.00072
Set of parts subject to wear pump	VST EVE-OG-25-40 10.03.02.00060
Oil	OEL EVE-OG 1L ANDEROL 555 27.02.01.00055
Oil filter	OEL-FILT EVE-OG-40-100G 10.03.02.00009
Sieve insert	SIEB-EINS 24x 41 NLS 10.01.27.01862
Pipe (machined)	ROHR 40x3x90 VC-SYS 10.01.27.00471
Horn	HUPE 42.5x43.5 S017 SW 21.05.05.00059
Accessories	ZUB BEL EVE-OG-40-AC3 22.09.03.00025

