


Art.-Nr.: 10.01.30.00477

**Technical data**

Attribute	Value
Material	Polyetheretherketon
Additional function area gripper	Quick-change adapter
Length L	100.00 mm
Width B	55.00 mm
Height H	26.90 mm

STGG 100x55x26.9 QCFA PEEK

Thin glass gripper STGG is delivered assembled.

Gripper available in various dimensions with integrated vacuum generation (1xE100 or QCMV) or with connection for external vacuum generation (QCM)

Available accessories: exhaust air set, holder system, suction / damping module, floating suction cup module, flange plate

Design data

Attribute	Value
Length L	100.00 mm
Width B	55.00 mm
Height H2	10.50 mm
Height H	26.90 mm
d2	14.0 mm
Thread G2	M4-F

Design data STGG 100x55x26.9 QCFA PEEK



Art.-Nr.: 10.01.30.00477

**Technical data**

Attribute	Value
Weight	120.0 g
Pressure range (operating pressure) [bar]	bar
Operating temperature	5 ... 60 °C
Air consumption	l/min
Suction rate	l/min
Holding force	N
Product family	STGG

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.00477

**Ordering Data Accessories 10.01.30.00477**

Typ		Item number
Holder system	HTR M12x1-IG SWGm	10.01.30.00119
Holder system	HTR M8x1-IG SWGm	10.01.30.00118
Holder system	HTR-UNI SWGm	10.01.30.00117
Floating suction cup module	SB5m 14 90-3 4/2 90	10.01.01.13171
Suction-/ Absorption module	SD-MOD 4 32x15x35 FG 9 SWGm	10.01.30.00121
Flange module	VEE-QCM 53	10.01.36.00122
Vacuum module	VEE-QCMV HV 2 07 13	10.01.36.00199

