


Suction cup (round)

SAUG-SCGS 30 SI-MD-55 602 B



Art.-Nr.: 10.01.30.01088



Technical data


Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	30.00

SAUG-SCGS 30 SI-MD-55 602 B

The flow gripper SCGS is constructed in two parts. To obtain a complete gripper (flow gripper + suction cup), the following ordering steps are necessary:

- Flow gripper (step1) – available for sideways mounting
- Suction cup (step 2)

Available accessories: screw in push fitting



Design data SAUG-SCGS 30 SI-MD-55 602 B

Design data

Attribute	Value
Height H	26.30 mm
Nominal diameter dn	15.00 mm
Thread G1	M20x1-F
Thread length LG1	5.0 mm
Spring stroke Z	5.5 mm
Diameter Ds	29.5 mm
Diameter Dmax(S)	32.5 mm
Diameter Dmax(N)	25.0 mm



WWW.SCHMALZ.COM/10.01.30.01088

Suction cup (round)

SAUG-SCGS 30 SI-MD-55 602 B



Art.-Nr.: 10.01.30.01088



Technical data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Weight	10.9 g
Size	30.00
Product family	SAUG-SCGS



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.30.01088



Ordering Data Spare Parts 10.01.30.01088

Typ	Item number
Bellows suction cup f SCG(S)-gripper BCG 30 SI-MD-55 SC085	10.01.06.04559



WWW.SCHMALZ.COM/10.01.30.01088