

Art.-Nr.: 10.01.38.02964



### Technical data

Attribute	Value
Construction vacuum switch	PNP switching
Weight	4.400 kg
Voltage DC	24 V - DC
Air consumption [l/min]	500.0 l/min
Design vacuum generator	Multi-stage ejector SEMP
Additional function area gripper	1x control valve vacuum / blow-off
Length L	838.00 mm
Width B	130.00 mm
Product family	FXP
Arrangement	5R18


FXP-S-SVK 838 5R18 N10SU

- Integrated control valves at FXP-S (optional)
- Control of vacuum on/off (24V DC, normally open) and blow off on/off (24V DC, normally closed) on version FXP-S
- Integrated in the end cover
- Electrical connection: M12 plug (4-pole)

Available spare parts: sealing foam (DI-PL), suction cup (SPB2)



Art.-Nr.: 10.01.38.02964



### Design data

Attribute	Value
Length L2	798.00 mm
Length L	838.00 mm
Width B	130.00 mm
Height H1	99.00 mm
Height H2	10.00 mm
Height H	60.00 mm
Length L3	154.00 mm
Width B3	21.60 mm
Height H3	7.70 mm
Height H4	5.50 mm
Hole spacing Y1	90.0 mm
Valve type	SVK
Height H5	28.00 mm

Permissible dimensional tolerances for elastomer parts according to DIN ISO 3302-1 M3 Note: Two ejectors and silencer box covers are used for the 1,234 mm and 1,432 mm lengths. Type FXP requires compressed air hose 12/9 mm.

Design data FXP-S-SVK 838 5R18 N10SU



### Technical data

Attribute	Value
Weight	4.400 kg
Air consumption [l/min]	500.0 l/min
Additional function area gripper	1x control valve vacuum / blow-off
Product family	FXP
Arrangement	5R18
Voltage	24V - DC
Sealing element	Sealing Foam

Sound level: 74 dB(A) Max. degree of evacuation 55 %



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.38.02964](http://www.schmalz.com/10.01.38.02964)

Art.-Nr.: 10.01.38.02964

**Discontinued item**

The product family will be discontinued and is available until **31.12.2027**  
Starting from this time, the article can no longer be ordered.  
alternative article

**Ordering Data Accessories 10.01.38.02964**

Typ		Item number
Flange plate	FLAN-PL 120x85x10 ST FLGR	10.01.10.05701
Flexolink	FLK G1/2-IG G1/2-AG	10.01.03.00175
Suspension, flexible	FST-FLEX 25 HD1 G1/2-AG G3/8-IG	10.01.10.05697
Suspension, flexible	FST-FLEX 25 HD2 G1/2-AG G3/8-IG	10.01.10.05695
Suspension, flexible	FST-FLEX 50 HD1 G1/2-AG G3/8-IG	10.01.10.05687
Suspension, flexible	FST-FLEX 50 HD2 G1/2-AG G3/8-IG	10.01.10.05168
Suspension, flexible	FST-FLEX 75 HD1 G1/2-AG G3/8-IG	10.01.10.05698
Suspension, flexible	FST-FLEX 75 HD2 G1/2-AG G3/8-IG	10.01.10.05696
Suspension, rigid	FST-STARR 25 HD1 G1/2-AG G3/8-IG	10.01.10.05810
Suspension, rigid	FST-STARR 25 HD2 G1/2-AG G3/8-IG	10.01.10.05806
Suspension, rigid	FST-STARR 50 HD1 G1/2-AG G3/8-IG	10.01.10.05809
Suspension, rigid	FST-STARR 50 HD2 G1/2-AG G3/8-IG	10.01.10.05805
Suspension, rigid	FST-STARR 75 HD1 G1/2-AG G3/8-IG	10.01.10.05808
Suspension, rigid	FST-STARR 75 HD2 G1/2-AG G3/8-IG	10.01.10.05803
Flange module	MOD-FLAN 120x120 FXP-FMP	10.01.21.00244
Flange module	MOD-FLAN 176.6x118 FXP	10.01.38.01722
Vacuum switch (inst)	VS-MONT 84x21x34.5 VSi-V FXP	10.01.38.02691
Mounting set reed switch	SET fuer-Sensor(FXP/FMP)	10.01.38.01194
Mounting set	SET FXC-FMC	10.01.21.01291
Mounting set	SET FXP-FMP	10.01.21.02407
Mounting set	SET FXP-FMP 4NUTSTEIN G20	10.01.21.00243
Vacuum gauge	VAM 40 V U BAR	10.07.02.00046
Vacuum hose (meter)	VSL 12-9 PU MI-TR	10.07.09.00037
Sliding block	NUT-STEI 20x20 M8-IG 10	25.09.06.00012
Sliding block	NUT-STEI 20x20 M6-IG 10	25.09.06.00036
Cover (complex)	ABDK-PROF-10x7x1450-KU-SW-FXP-FMP	26.07.03.00002
Connection cable	ASK B-M12-5 5000 K-5P	21.04.05.00080
Flange plate	FLAN-PL 120x120x10 FXC-FMC	10.01.21.00313
Flexolink	FLK G1/2-IG G1/2-AG V	10.01.03.00207
Vacuum switch (inst)	VS-MONT 84x21x34.5 VSi-V FXP	10.01.38.02691



Area Gripper

# FXP-S-SVK 838 5R18 N10SU



Art.-Nr.: 10.01.38.02964



## Ordering Data Spare Parts 10.01.38.02964

Typ		Item number
Set of spare parts	ERS FXP-S-SEMP-100 DECKEL	10.01.38.02192
Masking foil (glued)	MASK-FOL SVK 798 5R18 FXP-FMP	10.01.38.00522
Silencer (cube-shaped-inst.)	SD 120x79x29 FXP	10.01.38.01607



## Ordering Data Wear Parts 10.01.38.02964

Typ		Item number
Protective layer FLGR	SU-FLGR 838x131 SU FXP-FMP	10.01.38.02860
Seal. plate (FXP/FMP/FXP-S/FMP-S)	DI-PL 838x131 5R18 ZYL-D6 N10SU	10.01.38.02865



[WWW.SCHMALZ.COM/10.01.38.02964](http://WWW.SCHMALZ.COM/10.01.38.02964)