




SAXB 120 ED-85 G3/8-IG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



Tasarım verileri SAXB 120 ED-85 G3/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	120.00
Körük Sayısı	1.5
Bağlantı	G3/8-IG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	67.80 mm
Dış çap D1	95.0 mm
Dış G1	G3/8"-F
Dış uzunluğu LG1	13.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	32.0 mm
Çap Ds	120.6 mm
Çap Dmax(S)	131.0 mm

Art.-Nr.: 10.01.42.00009

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	8.0 mm
İř parası yarıapı dak (dışbükey)	67.5 mm
Emme kuvveti (-600mbar)	275.00 N
Ağırlık	115.0 g
Yanal kuvvet	479.0 N
Yanal kuvvet yağlı yüzey	380.0 N
Cilt	251.700 cm ³
Boyut	120.00
Körük Sayısı	1.5
Bađlantı	G3/8" -F
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00009

WWW.SCHMALZ.COM/10.01.42.00009