

Bellows suction cups (round)

SAXB 80 ED-85 RA



Art.-Nr.: 10.01.42.00017




SAXB 80 ED-85 RA

Bellows suction cup SAXB, available in various diameters, is supplied with a positively overmolded connection nipple.

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Size	80.00
Number of folds	1.5
Connection	RA
Nipple material	Aluminum



Design data SAXB 80 ED-85 RA

Design data

Attribute	Value
Height H	54.70 mm
Outside diameter D1	54.1 mm
Key width SW1	22.0 mm
Spring stroke Z	22.2 mm
Diameter Ds	81.0 mm
Length L4	31.80 mm
Diameter Dmax(S)	91.0 mm



Bellows suction cups (round)

SAXB 80 ED-85 RA



Art.-Nr.: 10.01.42.00017



Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	32.5 mm
Suction force (-600mbar)	150.00 N
Weight	54.20 g
Lateral force	176.0 N
Lateral force oily surface	155.0 N
Volume	70.700 cm ³
Size	80.00
Number of folds	1.5
Connection	Rectangular adapter
Product family	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00017



WWW.SCHMALZ.COM/10.01.42.00017