

Bellows suction cups (round)

SAXB 30 ED-85 G3/8-IG



Art.-Nr.: 10.01.42.00037




SAXB 30 ED-85 G3/8-IG

Bellows suction cup SAXB, available in various diameters, is supplied with a positively overmolded connection nipple.

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Size	30.00
Number of folds	1.5
Connection	G3/8-IG
Nipple material	Brass



Design data SAXB 30 ED-85 G3/8-IG

Design data

Attribute	Value
Height H	44.00 mm
Outside diameter D1	29.9 mm
Nominal diameter dn	4.10 mm
Thread G1	G3/8"-F
Thread length LG1	9.0 mm
Key width SW1	17.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	28.9 mm
Diameter Dmax(S)	33.0 mm



WWW.SCHMALZ.COM/10.01.42.00037

Bellows suction cups (round)

SAXB 30 ED-85 G3/8-IG



Art.-Nr.: 10.01.42.00037



Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	12.5 mm
Suction force (-600mbar)	24.00 N
Weight	43.0 g
Lateral force	24.0 N
Lateral force oily surface	20.0 N
Volume	5.300 cm ³
Size	30.00
Number of folds	1.5
Product family	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00037



WWW.SCHMALZ.COM/10.01.42.00037