

Bellows suction cups (round)

SAXB 50 ED-85 G1/4-IG



Art.-Nr.: 10.01.42.00051



SAXB 50 ED-85 G1/4-IG


Bellows suction cup SAXB, available in various diameters, is supplied with a positively overmolded connection nipple.

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Size	50.00
Number of folds	1.5
Connection	G1/4-IG
Nipple material	Brass

Design data

Attribute	Value
Height H	41.90 mm
Outside diameter D1	43.2 mm
Nominal diameter dn	6.10 mm
Thread G1	G1/4"-F
Thread length LG1	15.0 mm
Key width SW1	22.0 mm
Spring stroke Z	11.6 mm
Diameter Ds	49.6 mm
Diameter Dmax(S)	55.0 mm



Design data SAXB 50 ED-85 G1/4-IG



Art.-Nr.: 10.01.42.00051

**Technical data**

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	22.0 mm
Suction force (-600mbar)	58.00 N
Weight	39.6 g
Lateral force	78.0 N
Lateral force oily surface	67.0 N
Volume	18.900 cm ³
Size	50.00
Number of folds	1.5
Connection	G1/4" -F
Product family	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00051

