




SAXB 50 ED-85 G3/8-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.

## Teknik veriler

| Attribute                  | Value        |
|----------------------------|--------------|
| Vantuz malzemesi           | Elastodur ED |
| Malzeme sertliği [Shore A] | 85,0 Shore A |
| Boyut                      | 50,00        |
| Körük Sayısı               | 1,5          |
| Bağlantı                   | G3/8-AG      |
| Meme ucu malzemesi         | Alüminyum    |



Tasarım verileri SAXB 50 ED-85 G3/8-AG

## Tasarım verileri

| Attribute          | Value    |
|--------------------|----------|
| Yükseklik H        | 36,90 mm |
| Dış çap D1         | 43,2 mm  |
| Dış G1             | G3/8"-M  |
| Dış uzunluğu LG1   | 10,0 mm  |
| Anahtar boyutu SW1 | 22,0 mm  |
| Yay stroku Z       | 11,6 mm  |
| Çap Ds             | 49,6 mm  |
| Çap Dmax(S)        | 55,0 mm  |

Art.-Nr.: 10.01.42.00052

**Teknik veriler**

| Attribute                          | Value                  |
|------------------------------------|------------------------|
| Vantuz malzemesi                   | Elastodur ED           |
| Malzeme sertliği [Shore A]         | 85,0 Shore A           |
| Hortum çapı (tavsiye edilen) d     | 6,0 mm                 |
| İş parçası yarıçapı dak (dışbükey) | 22,0 mm                |
| Emme kuvveti (-600mbar)            | 58,00 N                |
| Ağırlık                            | 36,80 g                |
| Yanal kuvvet                       | 78,0 N                 |
| Yanal kuvvet yağlı yüzey           | 67,0 N                 |
| Cilt                               | 18,900 cm <sup>3</sup> |
| Boyut                              | 50,00                  |
| Körük Sayısı                       | 1,5                    |
| Bağlantı                           | G3/8"-M                |
| Ürün ailesi                        | SAXB                   |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.42.00052](http://www.schmalz.com/10.01.42.00052)

[WWW.SCHMALZ.COM/10.01.42.00052](http://WWW.SCHMALZ.COM/10.01.42.00052)