

Art.-Nr.: 10.01.42.00055




## Teknik veriler

| Attribute                  | Value        |
|----------------------------|--------------|
| Vantuz malzemesi           | Elastodur ED |
| Malzeme sertliği [Shore A] | 85.0 Shore A |
| Boyut                      | 100.00       |
| Körük Sayısı               | 1.5          |
| Bağlantı                   | G3/8-AG      |
| Meme ucu malzemesi         | Alüminyum    |

SAXB 100 ED-85 G3/8-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



## Tasarım verileri

| Attribute          | Value    |
|--------------------|----------|
| Yükseklik H        | 56.60 mm |
| Dış çap D1         | 78.4 mm  |
| Dış G1             | G3/8"-M  |
| Dış uzunluğu LG1   | 10.0 mm  |
| Anahtar boyutu SW1 | 22.0 mm  |
| Yay stroku Z       | 25.8 mm  |
| Çap Ds             | 99.6 mm  |
| Çap Dmax(S)        | 109.0 mm |

Tasarım verileri SAXB 100 ED-85 G3/8-AG



Art.-Nr.: 10.01.42.00055

**Teknik veriler**

| Attribute                          | Value                   |
|------------------------------------|-------------------------|
| Vantuz malzemesi                   | Elastodur ED            |
| Malzeme sertliđi [Shore A]         | 85.0 Shore A            |
| Hortum apı (tavsiye edilen) d     | 6.0 mm                  |
| İř parası yarıapı dak (dışbükey) | 45.0 mm                 |
| Emme kuvveti (-600mbar)            | 210.00 N                |
| Ağırlık                            | 82.5 g                  |
| Yanal kuvvet                       | 264.0 N                 |
| Yanal kuvvet yağlı yüzey           | 243.0 N                 |
| Cilt                               | 138.400 cm <sup>3</sup> |
| Boyut                              | 100.00                  |
| Körük Sayısı                       | 1.5                     |
| Bađlantı                           | G3/8"-M                 |
| Ürün ailesi                        | SAXB                    |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.42.00055](http://www.schmalz.com/10.01.42.00055)

[WWW.SCHMALZ.COM/10.01.42.00055](http://WWW.SCHMALZ.COM/10.01.42.00055)