




## Teknik veriler

| Attribute                  | Value        |
|----------------------------|--------------|
| Vantuz malzemesi           | Elastodur ED |
| Malzeme sertliği [Shore A] | 85,0 Shore A |
| Boyut                      | 100,00       |
| Körük Sayısı               | 1,5          |
| Bağlantı                   | M16-AG       |
| Meme ucu malzemesi         | Alüminyum    |

SAXB 100 ED-85 M16-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



## Tasarım verileri

| Attribute          | Value    |
|--------------------|----------|
| Yükseklik H        | 56,60 mm |
| Dış çap D1         | 78,4 mm  |
| Dış G1             | M16-M    |
| Dış uzunluğu LG1   | 11,0 mm  |
| Anahtar boyutu SW1 | 22,0 mm  |
| Yay stroku Z       | 25,8 mm  |
| Çap Ds             | 99,6 mm  |
| Çap Dmax(S)        | 109,0 mm |

Tasarım verileri SAXB 100 ED-85 M16-AG

**SAXB 100 ED-85 M16-AG**

Art.-Nr.: 10.01.42.00065

**Teknik veriler**

| Attribute                          | Value                   |
|------------------------------------|-------------------------|
| Vantuz malzemesi                   | Elastodur ED            |
| Malzeme sertliđi [Shore A]         | 85,0 Shore A            |
| Hortum apı (tavsiye edilen) d     | 4,0 mm                  |
| İř parası yarıapı dak (dışbükey) | 45,0 mm                 |
| Emme kuvveti (-600mbar)            | 210,00 N                |
| Ağırlık                            | 83,10 g                 |
| Yanal kuvvet                       | 240,0 N                 |
| Yanal kuvvet yağlı yüzey           | 243,0 N                 |
| Cilt                               | 138,400 cm <sup>3</sup> |
| Boyut                              | 100,00                  |
| Körük Sayısı                       | 1,5                     |
| Bağlantı                           | M16-M                   |
| Ürün ailesi                        | SAXB                    |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.42.00065](http://www.schmalz.com/10.01.42.00065)

[WWW.SCHMALZ.COM/10.01.42.00065](http://WWW.SCHMALZ.COM/10.01.42.00065)