



SAXB 20 ED-85 M16-AG


Bellows suction cup SAXB, available in various diameters, is supplied with a positively overmolded connection nipple.

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Size	20.00
Number of folds	1.5
Connection	M16-AG
Nipple material	Aluminum

Design data

Attribute	Value
Height H	25.00 mm
Outside diameter D1	20.6 mm
Thread G1	M16-M
Thread length LG1	11.0 mm
Key width SW1	17.0 mm
Spring stroke Z	5.8 mm
Diameter Ds	20.4 mm
Diameter Dmax(S)	23.5 mm



Design data SAXB 20 ED-85 M16-AG

Art.-Nr.: 10.01.42.00078

**Technical data**

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	8.0 mm
Suction force (-600mbar)	18.00 N
Weight	17.0 g
Lateral force	13.0 N
Lateral force oily surface	9.5 N
Volume	1.900 cm ³
Size	20.00
Number of folds	1.5
Connection	M16-M
Product family	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00078

