

Art.-Nr.: 10.01.42.00070




Technical data

Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Size	120.00
Number of folds	1.5
Connection	M16-AG
Nipple material	Aluminum

SAXB 120 ED-85 M16-AG

Bellows suction cup SAXB, available in various diameters, is supplied with a positively overmolded connection nipple.



Design data

Height H	67.80 mm
Outside diameter D1	95.0 mm
Thread G1	M16-M
Thread length LG1	11.0 mm
Key width SW1	22.0 mm
Spring stroke Z	32.0 mm
Diameter Ds	120.6 mm
Diameter Dmax(S)	131.0 mm

Design data SAXB 120 ED-85 M16-AG



Art.-Nr.: 10.01.42.00070

**Technical data**

Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	67.5 mm
Suction force (-600mbar)	275.00 N
Weight	126.00 g
Lateral force	479.0 N
Lateral force oily surface	380.0 N
Volume	251.700 cm ³
Size	120.00
Number of folds	1.5
Connection	M16-M
Product family	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

