

Art.-Nr.: 10.01.55.00003


**Technical data**

Max. vacuum	-850 mbar
Voltage at 50 Hz	190 - 255 V / 330 - 440 V AC3
Voltage at 60 Hz	190 - 290 V / 330 - 500 V AC3
Suction rate (max.)	25.000 m ³ /h
Reservoir volume	30.0 l
Design vacuum generator	Dry-running pump EVE-TR
Width B	457.00 mm
Height H	776.00 mm
with	Filter
Shape	Start

VH-TR Start 25 30

The vacuum unit VH-TR Start is delivered as a ready-to-connect product.

- Available spare parts: vacuum gauge, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set

**Design data**

Length L	521.00 mm
Width B	457.00 mm
Height H	776.00 mm
Outside diameter D	25.00 mm
with	Filter

Design data VH-TR Start 25 30



Art.-Nr.: 10.01.55.00003

**Technical data**

Max. vacuum	-850 mbar
Voltage at 50 Hz	190 - 255 V / 330 - 440 V AC3
Voltage at 60 Hz	190 - 290 V / 330 - 500 V AC3
Suction rate (max.)	25.000 m ³ /h
Reservoir volume	30.0 l

**Ordering Data Accessories 10.01.55.00003**

Typ		Item number
Vacuum hose (meter)	VSL 33-25 PVC-DS KL-TR	10.07.09.00041
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00003**

Typ		Item number
Vacuum pump	EVE-TR 25 AC3	10.03.01.00141
Vacuum gauge	VAM 67 V H-SE BAR/PSI	10.07.02.00016
Non-return valve	RSV 20 G3/4-IG MS	10.05.05.00004
Dust filter	STF G3/4-IG N	10.07.01.00007
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017

**Ordering Data Wear Parts 10.01.55.00003**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-25	10.03.01.00134

