

Art.-Nr.: 10.01.55.00005


**Technical data**

Max. vacuum	-850 mbar
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Suction rate (max.)	80.000 m ³ /h
Reservoir volume	100.0 l
Design vacuum generator	Dry-running pump EVE-TR
Width B	617.00 mm
Height H	858.00 mm
with	Filter
Shape	Start

VH-TR Start 80 100

The vacuum unit VH-TR Start is delivered as a ready-to-connect product.

- Available spare parts: vacuum gauge, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set

**Design data**

Length L	823.00 mm
Width B	617.00 mm
Height H	858.00 mm
Outside diameter D	38.00 mm
with	Filter

Design data VH-TR Start 80 100



Art.-Nr.: 10.01.55.00005

**Technical data**

Max. vacuum	-850 mbar
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Suction rate (max.)	80.000 m ³ /h
Reservoir volume	100.0 l

**Ordering Data Accessories 10.01.55.00005**

Typ		Item number
Vacuum hose (meter)	VSL 41-32 PVC-DS KL-TR	10.07.09.00008
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00005**

Typ		Item number
Vacuum pump	EVE-TR 80 AC3 IE3-TYP1	10.03.01.00321
Vacuum gauge	VAM 67 V H-SE BAR/PSI	10.07.02.00016
Non-return valve	RSV 36 G1-1/4-IG MS	10.05.05.00006
Dust filter	STF G1-1/4-IG N	10.07.01.00008
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018

**Ordering Data Wear Parts 10.01.55.00005**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR60/TR80	22.09.01.00031

