

Mounting profile (machined)

MO-PROF 25x30x1000 1TN AL



Art.-Nr.: 10.01.49.00089




MO-PROF 25x30x1000 1TN AL

Technical data

Attribute	Value
Length L	1,000.00 mm
Width B	25.00 mm
Height H	30.00 mm
Form	with 1 T-slot

Design data

Attribute	Value
Length L	1,000.00 mm
Width B	25.00 mm
Height H	30.00 mm



Design data MO-PROF 25x30x1000 1TN AL



Technical data

Attribute	Value
Material	Aluminum
Form	with 1 T-slot



WWW.SCHMALZ.COM/10.01.49.00089

Mounting profile (machined)

MO-PROF 25x30x1000 1TN AL



Art.-Nr.: 10.01.49.00089



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.49.00089



Ordering Data Accessories 10.01.49.00089

Typ		Artikelnummer
Tubing deburrer	ROHR-ENTGR VEE	10.01.36.00043
Tubing deburrer	ROHR-ENTGR PXT	10.01.49.00079
Holder profile tooling	HP-HT 2M8 56 HT-A3	10.07.06.00733
Holder profile for sensor	HP-SE-U 1M6 12/18	10.07.06.00719
Holder profile spring plunger	HP-FST 2M6 35 M18x1.5	10.07.06.00722
Holder profile spring plunger	HP-FST 2M6 35 M20x1.5	10.07.06.00723
Holder profile suction Cup	HP-SG 2M6 E 35 G1/4-AG	10.07.06.00712
Holder profile suction Cup	HP-SG 2M6 E 35 G3/8-AG	10.07.06.00715
Holder profile suction Cup	HP-SG 2M6 E 35 G1/4-IG	10.07.06.00716
Holder profile suction Cup	HP-SG 2M6 E 35 G3/8-IG	10.07.06.00717



WWW.SCHMALZ.COM/10.01.49.00089