

Art.-Nr.: 10.01.55.00001


**Technical data**

Max. vacuum	-850 mbar
Voltage at 50 Hz	D175 - 260 V / Y300 - 450 V
Voltage at 60 Hz	200 - 300 V or 350 - 520 V
Suction rate (max.)	10.000 m ³ /h
Reservoir volume	10.0 l
Design vacuum generator	Dry-running pump EVE-TR
Width B	457.00 mm
Height H	379.00 mm
with	Filter
Shape	Start

VH-TR Start 10 10

The vacuum unit VH-TR Start is delivered as a ready-to-connect product.

- Available spare parts: vacuum gauge, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set

**Design data**

Length L	673.00 mm
Width B	457.00 mm
Height H	379.00 mm
Outside diameter D	13.00 mm
with	Filter

Design data VH-TR Start 10 10



Art.-Nr.: 10.01.55.00001

**Technical data**

Max. vacuum	-850 mbar
Voltage at 50 Hz	D175 - 260 V / Y300 - 450 V
Voltage at 60 Hz	200 - 300 V or 350 - 520 V
Suction rate (max.)	10.000 m ³ /h
Reservoir volume	10.0 l

**Ordering Data Accessories 10.01.55.00001**

Typ		Item number
Accessories	ZUB VH 4CAS	10.01.27.02333
Vacuum hose (meter)	VSL 19-13 PVC-DS KL-TR	10.07.09.00016

**Ordering Data Spare Parts 10.01.55.00001**

Typ		Item number
Vacuum pump	EVE-TR 10 AC3	10.03.01.00137
Vacuum gauge	VAM 63 V H BAR/PSI	10.07.02.00003
Non-return valve	RSV 18 G1/2-IG MS	10.05.05.00003
Dust filter	STF G3/4-IG N	10.07.01.00007
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017

**Ordering Data Wear Parts 10.01.55.00001**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-10	10.03.01.00132

