

Art.-Nr.: 10.01.55.00009


**Technical data**

Max. vacuum	-850 mbar
Suction rate (max.)	25.000 m <sup>3</sup> /h
Additional function ejector	Vacuum switch digital
Reservoir volume	30.0 l
Design vacuum generator	Dry-running pump EVE-TR
Width B	457.00 mm
Height H	782.00 mm
Functionality of the ejector	electronic air-saving function
with	Filter
Shape	Plus

VH-TR Plus 25 30

The vacuum unit VH-TR Plus is delivered as a ready-to-connect product.

- Available spare parts: vacuum switch, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set

**Design data**

Length L	521.00 mm
Width B	457.00 mm
Height H	782.00 mm
Outside diameter D	25.00 mm
with	Filter

Design data VH-TR Plus 25 30



Art.-Nr.: 10.01.55.00009

**Technical data**

Max. vacuum	-850 mbar
Suction rate (max.)	25.000 m <sup>3</sup> /h
Additional function ejector	Vacuum switch digital
Reservoir volume	30.0 l
Functionality of the ejector	electronic air-saving function

**Ordering Data Accessories 10.01.55.00009**

Typ		Item number
Vacuum hose (meter)	VSL 33-25 PVC-DS KL-TR	10.07.09.00041
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00009**

Typ		Item number
Vacuum pump	EVE-TR 25 AC3	10.03.01.00141
Vacuum/pressure switch cube shape	VS-VP10-W-D M8-4 UH IOL	10.06.02.00883
Assembly set	SET VS EIN V/VP10 W-D	10.06.02.00863
Non-return valve	RSV 20 G3/4-IG MS	10.05.05.00004
Dust filter	STF G3/4-IG N	10.07.01.00007
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017

**Ordering Data Wear Parts 10.01.55.00009**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-25	10.03.01.00134

