

Art.-Nr.: 10.01.55.00014


**Technical data**

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V $\pm 10\%$
Voltage at 60 Hz	D265 V / Y460 V $\pm 10\%$
Suction rate (max.)	21.000 m <sup>3</sup> /h
Reservoir volume	30.0 l
Design vacuum generator	Oil-lubricated pump EVE-OG
Width B	457.00 mm
Height H	711.00 mm
with	Filter
Shape	Start

VH-OG Start 21 30

The vacuum unit VH-OG Start is delivered as a ready-to-connect product.

- Available spare parts: vacuum gauge, oil, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set

**Design data**

Length L	521.00 mm
Width B	457.00 mm
Height H	711.00 mm
Outside diameter D	25.00 mm
with	Filter

Design data VH-OG Start 21 30



Art.-Nr.: 10.01.55.00014

**Technical data**

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V $\pm 10$ %
Voltage at 60 Hz	D265 V / Y460 V $\pm 10$ %
Suction rate (max.)	21.000 m <sup>3</sup> /h
Reservoir volume	30.0 l

**Ordering Data Accessories 10.01.55.00014**

Typ		Item number
Vacuum hose (meter)	VSL 33-25 PVC-DS KL-TR	10.07.09.00041
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00014**

Typ		Item number
Vacuum pump	EVE-OG 21 AC3	10.03.02.00112
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Vacuum gauge	VAM 67 V H-SE BAR/PSI	10.07.02.00016
Dust filter	STF G3/4-IG N	10.07.01.00007
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017

**Ordering Data Wear Parts 10.01.55.00014**

Typ		Item number
Set of parts subject to wear pump	VST EVE-OG-21	10.03.02.00115

