

Art.-Nr.: 10.01.55.00010




VH-TR Plus 40 50

Technical data

Max. vacuum	-850 mbar
Voltage at 50 Hz	190 - 255 V / 330 - 440 V AC3
Voltage at 60 Hz	190 - 290 V / 330 - 500 V AC3
Suction rate (max.)	40.000 m ³ /h
Additional function ejector	Vacuum switch digital
Reservoir volume	50.0 l
Design vacuum generator	Dry-running pump EVE-TR
Width B	457.00 mm
Height H	782.00 mm
Functionality of the ejector	electronic air-saving function
with	Filter
Shape	Plus

The vacuum unit VH-TR Plus is delivered as a ready-to-connect product.

- Available spare parts: vacuum switch, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set



Design data VH-TR Plus 40 50

Design data

Length L	673.00 mm
Width B	457.00 mm
Height H	782.00 mm
Outside diameter D	25.00 mm
with	Filter



Art.-Nr.: 10.01.55.00010

**Technical data**

Max. vacuum	-850 mbar
Voltage at 50 Hz	190 - 255 V / 330 - 440 V AC3
Voltage at 60 Hz	190 - 290 V / 330 - 500 V AC3
Suction rate (max.)	40.000 m ³ /h
Additional function ejector	Vacuum switch digital
Reservoir volume	50.0 l
Functionality of the ejector	electronic air-saving function

**Ordering Data Accessories 10.01.55.00010**

Typ		Item number
Vacuum hose (meter)	VSL 41-32 PVC-DS KL-TR	10.07.09.00008
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00010**

Typ		Item number
Vacuum pump	EVE-TR 40 AC3	10.03.01.00142
Vacuum/pressure switch cube shape	VS-VP10-W-D M8-4 UH IOL	10.06.02.00883
Assembly set	SET VS EIN V/VP10 W-D	10.06.02.00863
Non-return valve	RSV 20 G3/4-IG MS	10.05.05.00004
Dust filter	STF G3/4-IG N	10.07.01.00007
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017

**Ordering Data Wear Parts 10.01.55.00010**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-40	10.03.01.00135

