

Art.-Nr.: 10.01.55.00015


**Technical data**

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V $\pm 10\%$
Voltage at 60 Hz	D265 V / Y460 V $\pm 10\%$
Suction rate (max.)	40.000 m ³ /h
Reservoir volume	50.0 l
Design vacuum generator	Oil-lubricated pump EVE-OG
Width B	457.00 mm
Height H	834.00 mm
with	Filter
Shape	Start

VH-OG Start 40 50

The vacuum unit VH-OG Start is delivered as a ready-to-connect product.

- Available spare parts: vacuum gauge, oil, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set

**Design data**

Length L	673.00 mm
Width B	457.00 mm
Height H	834.00 mm
Outside diameter D	32.00 mm
with	Filter

Design data VH-OG Start 40 50



Art.-Nr.: 10.01.55.00015

**Technical data**

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Suction rate (max.)	40.000 m ³ /h
Reservoir volume	50.0 l

**Ordering Data Accessories 10.01.55.00015**

Typ		Item number
Accessories	ZUB EVE-OG Ölablass-Kit	22.09.03.00038
Vacuum hose (meter)	VSL 41-32 PVC-DS KL-TR	10.07.09.00008
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00015**

Typ		Item number
Vacuum pump	EVE-OG 40 AC3	10.03.02.00026
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Vacuum gauge	VAM 67 V H-SE BAR/PSI	10.07.02.00016
Dust filter	STF G1-1/4-IG N	10.07.01.00008
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018

**Ordering Data Wear Parts 10.01.55.00015**

Typ		Item number
Set of parts subject to wear pump	VST EVE-OG-25-40	10.03.02.00060

