

Feed ejector SEC-100



Art.-Nr.: 10.02.01.00078




SEC-100

Feed ejector SEC is delivered as a ready-to-connect product.

Technical data

Attribute	Value
Suction rate (max.)	36.600 m ³ /h

Design data



Attribute	Value
Length L1	70.00 mm
Length L	21.00 mm
Outside diameter D1	19.0 mm
Outside diameter D2	19.0 mm
Outside diameter D	37.00 mm
Thread G2	G1/8"-F
Thread length LG3	8.0 mm
Hole spacing X1	29.0 mm
Thread G3	M4-F

Design data SEC-100



WWW.SCHMALZ.COM/10.02.01.00078

Feed ejector SEC-100



Art.-Nr.: 10.02.01.00078



Technical data

Attribute	Value
Max. vacuum	-5.020 inHg
Weight	0.070 kg
Air consumption suction	6.709 cfm
Suction rate (max.)	21.541 cfm
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	-20 ... 80 °C
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.00078



WWW.SCHMALZ.COM/10.02.01.00078