

Feed ejector  
**SEC-200**




Art.-Nr.: 10.02.01.00079



SEC-200

Feed ejector SEC is delivered as a ready-to-connect product.



Design data SEC-200

**Technical data**

| Attribute           | Value                    |
|---------------------|--------------------------|
| Suction rate (max.) | 82.500 m <sup>3</sup> /h |

**Design data**

| Attribute           | Value    |
|---------------------|----------|
| Length L1           | 90.00 mm |
| Length L            | 30.00 mm |
| Outside diameter D1 | 38.0 mm  |
| Outside diameter D2 | 32.0 mm  |
| Outside diameter D  | 50.00 mm |
| Thread G2           | G1/4"-F  |
| Thread length LG3   | 12.0 mm  |
| Hole spacing X1     | 42.0 mm  |
| Thread G3           | M4-F     |



[WWW.SCHMALZ.COM/10.02.01.00079](http://WWW.SCHMALZ.COM/10.02.01.00079)

Feed ejector  
**SEC-200**



Art.-Nr.: 10.02.01.00079



**Technical data**

| Attribute                                 | Value         |
|-------------------------------------------|---------------|
| Max. vacuum                               | -1.771 inHg   |
| Weight                                    | 0.180 kg      |
| Air consumption suction                   | 10.241 cfm    |
| Suction rate (max.)                       | 48.380 cfm    |
| Pressure range (operating pressure) [bar] | 29.0 ... 87.0 |
| Operating temperature                     | -20 ... 80 °C |
| Product family                            | SEC           |

Note: Air consumption: At optimal operating pressure (4,5 bar)



**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.02.01.00079](http://www.schmalz.com/10.02.01.00079)



[WWW.SCHMALZ.COM/10.02.01.00079](http://WWW.SCHMALZ.COM/10.02.01.00079)