

Art.-Nr.: 10.01.55.00020




VH-OG Plus 21 30

## Technical data

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V $\pm 10$ %
Voltage at 60 Hz	D265 V / Y460 V $\pm 10$ %
Suction rate (max.)	21.000 m <sup>3</sup> /h
Additional function ejector	Vacuum switch digital
Reservoir volume	30.0 l
Design vacuum generator	Oil-lubricated pump EVE-OG
Width B	457.00 mm
Height H	711.00 mm
Functionality of the ejector	electronic air-saving function
with	Filter
Shape	Plus

The vacuum unit VH-OG Plus is delivered as a ready-to-connect product.

- Available spare parts: vacuum switch, oil, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set



Design data VH-OG Plus 21 30

## Design data

Length L	521.00 mm
Width B	457.00 mm
Height H	711.00 mm
Outside diameter D	25.00 mm
with	Filter

Art.-Nr.: 10.01.55.00020

**Technical data**

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V $\pm 10$ %
Voltage at 60 Hz	D265 V / Y460 V $\pm 10$ %
Suction rate (max.)	21.000 m <sup>3</sup> /h
Additional function ejector	Vacuum switch digital
Reservoir volume	30.0 l
Functionality of the ejector	electronic air-saving function

**Ordering Data Accessories 10.01.55.00020**

Typ		Item number
Vacuum hose (meter)	VSL 33-25 PVC-DS KL-TR	10.07.09.00041
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00020**

Typ		Item number
Vacuum pump	EVE-OG 21 AC3	10.03.02.00112
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Vacuum/pressure switch cube shape	VS-VP10-W-D M8-4 UH IOL	10.06.02.00883
Dust filter	STF G3/4-IG N	10.07.01.00007
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017

**Ordering Data Wear Parts 10.01.55.00020**

Typ		Item number
Set of parts subject to wear pump	VST EVE-OG-21	10.03.02.00115

