

Feed ejector
SEC-400




Art.-Nr.: 10.02.01.00080



SEC-400

Feed ejector SEC is delivered as a ready-to-connect product.



Design data SEC-400

Technical data

Attribute	Value
Suction rate (max.)	135.000 m ³ /h

Design data

Attribute	Value
Length L1	95.00 mm
Length L	35.00 mm
Outside diameter D1	75.0 mm
Outside diameter D2	52.0 mm
Outside diameter D	84.00 mm
Thread G2	G3/8"-F
Thread length LG3	14.0 mm
Hole spacing X1	72.0 mm
Thread G3	M4-F



WWW.SCHMALZ.COM/10.02.01.00080

Feed ejector
SEC-400



Art.-Nr.: 10.02.01.00080



Technical data

Attribute	Value
Max. vacuum	-0.738 inHg
Weight	0.525 kg
Air consumption suction	17.657 cfm
Suction rate (max.)	79.456 cfm
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	-20 ... 80 °C
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.00080



WWW.SCHMALZ.COM/10.02.01.00080