

Feed ejector
SEC-750




Art.-Nr.: 10.02.01.00081



SEC-750

Feed ejector SEC is delivered as a ready-to-connect product.



Design data SEC-750

Technical data

Attribute	Value
Suction rate (max.)	518.400 m ³ /h

Design data

Attribute	Value
Length L1	180.00 mm
Length L	65.00 mm
Outside diameter D1	125.0 mm
Outside diameter D2	100.0 mm
Outside diameter D	140.00 mm
Thread G2	G1/2"-F
Thread length LG3	6.0 mm
Hole spacing X1	126.0 mm
Thread G3	M6-F



WWW.SCHMALZ.COM/10.02.01.00081

Feed ejector
SEC-750



Art.-Nr.: 10.02.01.00081



Technical data

Attribute	Value
Max. vacuum	-0.147 inHg
Weight	2.350 kg
Air consumption suction	27.191 cfm
Suction rate (max.)	305.112 cfm
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	-20 ... 80 °C
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.00081



WWW.SCHMALZ.COM/10.02.01.00081