

Basic Ejector SEG 20 HS



Art.-Nr.: 10.02.01.00256




Technical data

Nozzle diameter	2.0 mm
Air consumption suction	186.0 l/min
Suction rate (max.)	124.0 l/min
Shape	For high vacuum

SEG 20 HS

The basic ejector SEG is delivered as a ready-to-connect product.

Available spare parts: silencer



Design data

Length L	90.00 mm
Width B	26.00 mm
Height H	38.00 mm
Outside diameter D	20.00 mm
Thread G1	G1/4"-F
Thread G2	G1/4"-F
Key width SW1	17.0 mm
Thread G3	G3/8"-F

Design data SEG 20 HS



WWW.SCHMALZ.COM/10.02.01.00256

Art.-Nr.: 10.02.01.00256

**Technical data**

Nozzle diameter	2.0 mm
Recommended hose internal diameter compressed air	4.0 mm
Recommended hose internal diameter vacuum	9.0 mm
Degree of evacuation	85.0 %
Weight	118.00 g
Air consumption suction	6.568 cfm
Suction rate (max.)	4.378 cfm
Optimal operating pressure	5.00 bar
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Operating temperature	-10 ... 80 °C
Pressure range (operating pressure) [psi]	43.5 ... 87.0
Optimal pressure	72.5 psi
Product family	SEG


Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m




Art.-Nr.: 10.02.01.00256




Performance data



Achievable vacuum at various operating pressures



Evacuation time for various vacuum ranges [s/l]



Suction rate at various degrees of evacuation [l/min]



Achievable vacuum at various operating pressures

	2.5	3	3.5	4	4.5	5	5.5	6
SEG HS	400.00	500.00	610.00	720.00	825.00	870.00	885.00	880.00
SEG LS	270.00	325.00	390.00	450.00	510.00	520	520	520



Art.-Nr.: 10.02.01.00256



Evacuation time for various vacuum ranges [s/l]

	50	100	200	300	400	500	600	700	800
SEG 20 HS	0.03	0.05	0.11	0.16	0.24	0.35	0.50	1.08	1.65
SEG 25 HS	0.01	0.03	0.06	0.09	0.14	0.20	0.3	0.49	1.10
SEG 30 HS	0.01	0.02	0.04	0.06	0.10	0.15	0.21	0.42	0.80



Suction rate at various degrees of evacuation [l/min]

	0	50	100	200	300	400	500	600	700	800
SEG 20 HS	124	116	104	92	78	64	48	32	23	10
SEG 25 HS	184	180	170	146	120	96	72	47	28	13
SEG 30 HS	240	225	215	198	165	130	100	64	36	16



Ordering Data Accessories 10.02.01.00256

Typ	Item number
Vacuum cup filter	VFT G1/4-IG 100 10.07.01.00120

