

Inline ejector
SLP 05 S01



Art.-Nr.: 10.02.01.00561



SLP 05 S01


Inline ejector SLP is delivered as a ready-to-connect product.

Technical data

Attribute	Value
Nozzle diameter	0.5 mm
Degree of evacuation	85.0 %
Air consumption suction	13.0 l/min
Suction rate (max.)	8.0 l/min
Optimal operating pressure	4.50 bar
Connection	Hose D4(1)-D4(2)

Design data

Attribute	Value
Length L	57.00 mm
Outside diameter D	10.00 mm
Internal diameter d	4.00 mm



Design data SLP 05 S01



WWW.SCHMALZ.COM/10.02.01.00561

Art.-Nr.: 10.02.01.00561



Technical data

Attribute	Value
Nozzle diameter	0.5 mm
Recommended hose internal diameter compressed air	2.0 mm
Recommended hose internal diameter vacuum	2.0 mm
Degree of evacuation	85.0 %
Sound pressure level suction	52.0 dB(A)
Sound pressure level free	60.0 dB(A)
Weight	5.0 g
Air consumption suction	0.459 cfm
Suction rate (max.)	0.282 cfm
Optimal operating pressure	4.50 bar
Operating temperature	0 ... 60 °C
Optimal pressure	65.2 psi
Product family	SLP

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.00561

