

Inline ejector
SLP 07 S01



Art.-Nr.: 10.02.01.00562



SLP 07 S01


Inline ejector SLP is delivered as a ready-to-connect product.

Technical data

Attribute	Value
Nozzle diameter	0.7 mm
Degree of evacuation	85.0 %
Air consumption suction	25.0 l/min
Suction rate (max.)	15.9 l/min
Optimal operating pressure	4.50 bar
Connection	Hose D4(1)-D4(2)

Design data

Attribute	Value
Length L	57.00 mm
Outside diameter D	10.00 mm
Internal diameter d	4.00 mm



Design data SLP 07 S01



Art.-Nr.: 10.02.01.00562



Technical data

Attribute	Value
Nozzle diameter	0.7 mm
Recommended hose internal diameter compressed air	2.0 mm
Recommended hose internal diameter vacuum	2.0 mm
Degree of evacuation	85.0 %
Sound pressure level suction	63.0 dB(A)
Sound pressure level free	63.0 dB(A)
Weight	5.0 g
Air consumption suction	0.882 cfm
Suction rate (max.)	0.561 cfm
Optimal operating pressure	4.50 bar
Operating temperature	0 ... 60 °C
Optimal pressure	65.2 psi
Product family	SLP

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.00562

