

Feed ejector SEC-60




Art.-Nr.: 10.02.01.01079



SEC-60

Feed ejector SEC is delivered as a ready-to-connect product.



Design data SEC-60

Technical data

Attribute	Value
Material	Aluminum
Suction rate (max.)	12.900 m ³ /h

Design data

Attribute	Value
Length L1	44.00 mm
Length L	14.00 mm
Outside diameter D1	12.5 mm
Outside diameter D2	12.5 mm
Outside diameter D	32.00 mm
Thread G2	M5-F
Thread length LG3	5.0 mm
Hole spacing X1	25.0 mm
Thread G3	M3-F



WWW.SCHMALZ.COM/10.02.01.01079

Feed ejector SEC-60



Art.-Nr.: 10.02.01.01079



Technical data

Attribute	Value
Max. vacuum	-7.234 inHg
Weight	0.040 kg
Material	Aluminum
Air consumption suction	4.943 cfm
Suction rate (max.)	7.592 cfm
Pressure range (operating pressure) [bar]	29.0 ... 72.5
Operating temperature	°C
Product family	SEC
Note: Air consumption: At optimal operating pressure (4,5 bar)	



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01079



WWW.SCHMALZ.COM/10.02.01.01079