




SEC-200 A2

Feed ejector SEC is delivered as a ready-to-connect product.



Design data SEC-200 A2

Technical data

Attribute	Value
Material	Austenitic stainless steel
Suction rate (max.)	82.500 m ³ /h

Design data

Attribute	Value
Length L1	90.00 mm
Length L	30.00 mm
Outside diameter D1	38.0 mm
Outside diameter D2	32.0 mm
Outside diameter D	50.00 mm
Thread G2	G1/4"-F
Thread length LG3	12.0 mm
Hole spacing X1	42.0 mm
Thread G3	M4-F

Art.-Nr.: 10.02.01.01326

**Technical data**

Attribute	Value
Max. vacuum	-1.771 inHg
Weight	0.511 kg
Material	Austenitic stainless steel
Air consumption suction	10.241 cfm
Suction rate (max.)	48.380 cfm
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	°C
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01326