

Basic Ejector

SBP-C 10 G02 NO A VS-T



Art.-Nr.: 10.02.01.01008



Technical data

Nozzle diameter	1.0 mm
Degree of evacuation	85.0 %
Air consumption suction	48.0 l/min
Suction rate (max.)	35.0 l/min
Optimal operating pressure	4.50 bar
Connection	G 1/8" (1)-G 1/8" (2)
Shape compact ejectors	Blow-off function
Control valve	Normally open
Functionality of the ejector	electronic vacuum switch

SBP-C 10 G02 NO A VS-T

The basic ejector SBP-C is delivered as a ready-to-connect product (without connection cable).

Available spare parts: silencer


Available accessories: mounting plate, mounting set, connection cable



WWW.SCHMALZ.COM/10.02.01.01008

1

Art.-Nr.: 10.02.01.01008



Design data

Length L1	146.00 mm
Length L2	19.00 mm
Length L	106.00 mm
Width B	15.00 mm
Height H1	50.00 mm
Height H2	5.20 mm
Height H	51.00 mm
Outside diameter D	13.50 mm
Internal diameter d	4.20 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-F
Key width SW1	14.0 mm
Spanner size SW2	14.0 mm
Length L3	29.50 mm
Height H3	8.50 mm
Height H4	11.80 mm
Hole spacing X1	20.0 mm
Thread G3	G1/8"-F

Design data SBP-C 10 G02 NO A VS-T



Technical data

Nozzle diameter	1.0 mm
Recommended hose internal diameter compressed air	4.0 mm
Recommended hose internal diameter vacuum	6.0 mm
Degree of evacuation	85.0 %
Sound pressure level suction	59.0 dB(A)
Sound pressure level free	65.0 dB(A)
Weight	145.00 g
Air consumption suction	1.695 cfm
Suction rate (max.)	1.235 cfm
Optimal operating pressure	4.50 bar
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Operating temperature	0 ... 50 °C
Pressure range (operating pressure) [psi]	43.5 ... 87.0
Air consumption blow-off	1.059 cfm
Optimal pressure	65.2 psi
Product family	SBP-C


Note: The supply voltage for vacuum switches and solenoid valves is 24 VDC Air consumption: On version with solenoid valves SBP-C 07 (24) / SBP-C 25 (320) and optimal operating pressure Hose diameter: For max. length 2 m




Art.-Nr.: 10.02.01.01008




Performance data



Achievable vacuum at various operating pressures



Evacuation time for various vacuum ranges [s/l]



Suction rate at various degrees of evacuation [l/min]



Achievable vacuum at various operating pressures

	2	3	4	5	6
SBP-C	350.00	575.00	790.00	860.00	830.00



Art.-Nr.: 10.02.01.01008

**Evacuation time for various vacuum ranges [s/l]**

	50	100	200	300	400	500	600	700	800
SBP-C 05	0.34	0.68	1.56	2.66	4.02	5.84	8.54	13.22	25.54
SBP-C 07	0.20	0.38	0.84	1.46	2.24	3.26	4.66	6.84	12.56
SBP-C 10	0.06	0.14	0.30	0.52	0.82	1.30	1.98	3.26	6.56
SBP-C 15	0.05	0.08	0.16	0.26	0.40	0.60	0.86	1.30	2.54
SBP-C 20	0.03	0.05	0.09	0.16	0.24	0.34	0.49	0.80	1.74
SBP-C 25	0.02	0.03	0.06	0.09	0.14	0.20	0.28	0.42	0.99

**Suction rate at various degrees of evacuation [l/min]**

	0	50	100	200	300	400	500	600	700	800
SBP-C 05	7.00	6.20	5.30	4.50	3.70	3.00	2.20	1.40	0.40	0.10
SBP-C 07	16.00	13.60	11.37	9.03	7.25	5.63	3.97	2.65	1.10	0.30
SBP-C 10	38.00	33.20	30.10	26.70	23.00	18.60	14.90	9.80	5.20	1.61
SBP-C 15	70.00	65.00	60.10	52.00	44.00	36.50	29.00	20.50	11.40	2.18
SBP-C 20	123.00	115.00	104.00	93.00	78.00	64.00	49.00	35.50	23.00	8.00
SBP-C 25	215.00	175.00	157.50	139.50	119.00	99.50	79.60	59.00	37.30	16.30

**Ordering Data Accessories 10.02.01.01008**

Typ		Item number
Mounting plate	BEF-PL 110x44.5x3 SBP	10.02.01.00511
Mounting set	SET SBP M4-IG	10.02.01.00769
Connection cable	ASK B-MIC10 3000 K-2P	21.04.06.00086
Connection cable	ASK B-M8-4 5000 K-4P	10.06.02.00031
Vacuum filter (inline)	VFI CN8/6 50	10.07.01.00245
Vacuum filter (inline)	VFI 6/4 50	10.07.01.00328
Vacuum cup filter	VFT G1/8-IG 80	10.07.01.00116
Basic Ejector	SEG 10 HS	10.02.01.00247

**Ordering Data Spare Parts 10.02.01.01008**

Typ		Item number
Silencer (round)	SD G1/8-AG 14x40	10.02.01.00540
Vacuum/pressure switch teachfunction	VS-V-AH-T-PNP M8-4 S	10.06.02.00294

