

Basic Ejector

SBPL 150 HF



Art.-Nr.: 10.02.01.01599




SBPL 150 HF

The basic ejector SBPL is delivered as a ready-to-connect product.

Available accessories: retrofit kit, sealing plugs, vacuum manometer, quick exhaust valves, exhaust kit, retrofit kit, solenoid valves, vacuum cup filter, mounting brackets, vacuum hose, hose nozzle

Technical data

Attribute	Value
Weight	1.500 kg
Air consumption suction	435.0 l/min
Suction rate (max.)	1,120.0 l/min
Size	150.00
Shape	High flow



Design data SBPL 150 HF

Design data


Attribute	Value
Length L1	285.30 mm
Length L2	54.00 mm
Length L	167.50 mm
Width B2	16.00 mm
Width B	115.00 mm
Height H1	74.00 mm
Height H	72.00 mm
Thread G1	G3/8"-F
Thread G2	G1"-F
Length L4	113.00 mm




Art.-Nr.: 10.02.01.01599

**Technical data**

Attribute	Value
Recommended hose internal diameter compressed air	11.0 mm
Recommended hose internal diameter vacuum	32.0 mm
Degree of evacuation	60.0 %
Max. vacuum	17.718 inHg
Sound pressure level suction	61.0 dB(A)
Sound pressure level free	71.0 dB(A)
Weight	1.500 kg
Air consumption suction	26.750 m ³ /h
Suction rate (max.)	1,120.0 l/min
Size	150.00
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	0 ... 60 °C
Suction rate	117.000 m ³ /h
Product family	SBPL

**Performance data**

Achievable vacuum at various operating pressures



Suction rate at various degrees of evacuation [l/min]

**Achievable vacuum at various operating pressures**

	2	3	4	5	6
SBPL ... HV	350.00	600.00	900.00	910.00	911.00
SBPL ... HF	320.00	460.00	610.00	720.00	740.00



Art.-Nr.: 10.02.01.01599

**Suction rate at various degrees of evacuation [l/min]**

	0	50	100	200	300	400	500	600
SBPL 100 HF	860	680	570	465	305	190	125	50
SBPL 125 HF	1010	820	720	580	380	235	150	60
SBPL 150 HF	1120	890	805	670	425	275	175	70

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01599**Ordering Data Accessories 10.02.01.01599**

Typ		Item number
Mouting bracket (inst.)	BEF-WIN 72x25x77 SBPL/SCPL	10.02.01.01705
Vacuum gauge (electronic)	VAM-D 30x30 VP10 G1/8-AG	10.07.02.00055
Vacuum gauge	VAM 40 V DR BAR	10.07.02.00035
Vacuum/pressure switch	VSi V D M8-4	10.06.02.00577
Solenoid valve pressure	EMV 3 24V-DC 2/2 NC K-2P	10.05.01.00366
Quick release valve	SEV G1/8-IG G1/4-AG	10.02.01.01471
Hose sleeve	ST 32 AL-EL	10.02.01.01681
Vacuum hose (meter)	VSL 27-20 PU-DS-AS TR	10.07.09.00047
Vacuum hose (meter)	VSL 32-25 PU-DS-AS TR	10.07.09.00051
Vacuum hose (meter)	VSL 42-32 PU-DS-AS TR	10.07.09.00036
Exhaust air set	ABL-SET SBPL/SCPL M	10.02.01.01939
Dust filter	STF G1-1/4-IG N	10.07.01.00008

**Ordering Data Spare Parts 10.02.01.01599**

Typ		Item number
Set of spare parts	ERS SEP-22 6xRUE-KLAP	10.02.01.01450
Silencer (cube-shaped-inst.)	SD 102x71x33 SBPL/SCPL	10.02.01.01585
Ejector module	SEP HF 3 13 22	10.02.01.01348



Basic Ejector

SBPL 150 HF



Art.-Nr.: 10.02.01.01599



Ordering Data Wear Parts 10.02.01.01599

Typ		Item number
Sealing frame	DI-RA 112.5x34.8 NBR-55 SBPL/SCPL	10.02.01.01541
Set of spare parts	ERS SEP-22 6xRUE-KLAP	10.02.01.01450
O-ring	O-RING 10x2.5 NBR-70	10.07.08.00002



WWW.SCHMALZ.COM/10.02.01.01599