

Art.-Nr.: 10.02.01.01590




Technical data

Attribute	Value
Weight	0.750 kg
Air consumption suction	210.0 l/min
Suction rate (max.)	510.0 l/min
Size	50.00
Shape	High vacuum

SBPL 50 HV

The basic ejector SBPL is delivered as a ready-to-connect product.

Available accessories: retrofit kit, sealing plugs, vacuum manometer, quick exhaust valves, exhaust kit, retrofit kit, solenoid valves, vacuum cup filter, mounting brackets, vacuum hose, hose nozzle



Design data

Attribute	Value
Length L1	285.30 mm
Length L2	54.00 mm
Length L	167.50 mm
Width B2	16.00 mm
Width B	51.00 mm
Height H1	74.00 mm
Height H	72.00 mm
Thread G1	G3/8"-F
Thread G2	G3/4"-F
Length L4	113.00 mm

Design data SBPL 50 HV

Art.-Nr.: 10.02.01.01590

**Technical data**


Attribute	Value
Recommended hose internal diameter compressed air	6.0 mm
Recommended hose internal diameter vacuum	25.0 mm
Degree of evacuation	90.0 %
Max. vacuum	26.577 inHg
Sound pressure level suction	59.0 dB(A)
Sound pressure level free	66.0 dB(A)
Weight	0.750 kg
Air consumption suction	13.000 m ³ /h
Suction rate (max.)	510.0 l/min
Size	50.00
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	0 ... 60 °C
Suction rate	39.600 m ³ /h
Product family	SBPL




Art.-Nr.: 10.02.01.01590




Performance data



Achievable vacuum at various operating pressures



Evacuation time for various vacuum ranges [s/l]



Suction rate at various degrees of evacuation [l/min]



Achievable vacuum at various operating pressures

	2	3	4	5	6
SBPL ... HV	350.00	600.00	900.00	910.00	911.00
SBPL ... HF	320.00	460.00	610.00	720.00	740.00



Art.-Nr.: 10.02.01.01590

**Evacuation time for various vacuum ranges [s/l]**

	0	100	200	300	400	500	600	700	800
SBPL 25 HV	-	0.04	0.08	0.12	0.19	0.32	0.54	0.84	1.38
SBPL 50 HV	-	0.03	0.05	0.07	0.11	0.18	0.28	0.43	0.71
SBPL 75 HV	-	0.02	0.03	0.05	0.07	0.12	0.18	0.28	0.46

**Suction rate at various degrees of evacuation [l/min]**

	0	50	100	200	300	400	500	600	700	800
SBPL 25 HV	300	225	150	125	100	70	50	35	20	8
SBPL 50 HV	510	400	300	230	190	120	70	55	35	15
SBPL 75 HV	720	540	400	340	270	165	100	83	57	25

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01590**Ordering Data Accessories 10.02.01.01590**

Typ		Item number
Mouting bracket (inst.)	BEF-WIN 72x25x77 SBPL/SCPL	10.02.01.01705
Vacuum gauge (electronic)	VAM-D 30x30 VP10 G1/8-AG	10.07.02.00055
Vacuum gauge	VAM 40 V DR BAR	10.07.02.00035
Vacuum/pressure switch	VSi V D M8-4	10.06.02.00577
Solenoid valve pressure	EMV 3 24V-DC 2/2 NC K-2P	10.05.01.00366
Quick release valve	SEV G1/8-IG G1/4-AG	10.02.01.01471
Hose sleeve	ST 25 AL-EL	10.02.01.01680
Vacuum hose (meter)	VSL 27-20 PU-DS-AS TR	10.07.09.00047
Vacuum hose (meter)	VSL 32-25 PU-DS-AS TR	10.07.09.00051
Vacuum hose (meter)	VSL 42-32 PU-DS-AS TR	10.07.09.00036
Exhaust air set	ABL-SET SBPL/SCPL M	10.02.01.01939
Exhaust air set	ABL-SET SBPL/SCPL L	10.02.01.01940
Vacuum cup filter	VFT G3/4-IG 80	10.07.01.00128
Retrofitting kit	SET SBPL 75/100	10.02.01.01685



Art.-Nr.: 10.02.01.01590

**Ordering Data Spare Parts 10.02.01.01590**

Typ		Item number
Set of spare parts	ERS SEP-22 6xRUE-KLAP	10.02.01.01450
Silencer (cube-shaped-inst.)	SD 102x71x33 SBPL/SCPL	10.02.01.01585
Ejector module	SEP HV 3 16 22	10.02.01.01397

**Ordering Data Wear Parts 10.02.01.01590**

Typ		Item number
Sealing frame	DI-RA 112.5x34.8 NBR-55 SBPL/SCPL	10.02.01.01541
Set of spare parts	ERS SEP-22 6xRUE-KLAP	10.02.01.01450
O-ring	O-RING 10x2.5 NBR-70	10.07.08.00002

