




Technical data

Attribute	Value
Material	Austenitic stainless steel
Suction rate (max.)	135.000 m³/h

SEC-400 A2

Feed ejector SEC is delivered as a ready-to-connect product.



Design data

Attribute	Value
Length L1	95.00 mm
Length L	35.00 mm
Outside diameter D1	75.0 mm
Outside diameter D2	52.0 mm
Outside diameter D	84.00 mm
Thread length LG3	14.0 mm
Hole spacing X1	72.0 mm
Thread G3	M4-F

Design data SEC-400 A2

Art.-Nr.: 10.02.01.01620

**Technical data**

Attribute	Value
Max. vacuum	-0.738 inHg
Weight	1.475 kg
Material	Austenitic stainless steel
Air consumption suction	17.657 cfm
Suction rate (max.)	79.456 cfm
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	°C
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01620