

Feed ejector SEC-100 A2



Art.-Nr.: 10.02.01.01691




SEC-100 A2

Feed ejector SEC is delivered as a ready-to-connect product.

Technical data

Attribute	Value
Material	Austenitic stainless steel
Suction rate (max.)	36.600 m ³ /h

Design data



Attribute	Value
Length L1	70.00 mm
Length L	21.00 mm
Outside diameter D1	19.0 mm
Outside diameter D2	19.0 mm
Outside diameter D	37.00 mm
Thread length LG3	8.0 mm
Hole spacing X1	29.0 mm
Thread G3	M4-F

Design data SEC-100 A2



WWW.SCHMALZ.COM/10.02.01.01691

Art.-Nr.: 10.02.01.01691

**Technical data**

Attribute	Value
Max. vacuum	-5.020 inHg
Weight	0.206 kg
Material	Austenitic stainless steel
Air consumption suction	6.709 cfm
Suction rate (max.)	21.541 cfm
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	°C
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01691