



Art.-Nr.: 10.02.01.01729



SBP HF 2 06 13 SD

The basic ejectors SBP-HV/HF is delivered as a ready-to-connect product.



Design data SBP HF 2 06 13 SD

Technical data

Attribute	Value
Nozzle diameter	0.6 mm
Degree of evacuation	70.0 %
Air consumption suction	18.7 l/min
Suction rate (max.)	42.5 l/min
Additional function ejector	Silencer
Size	13.00
Optimal operating pressure	4.00 bar
Number of stages	2
Shape	High flow

Design data

Attribute	Value
Length L1	121.00 mm
Length L2	22.00 mm
Length L	69.50 mm
Width B	23.00 mm
Height H2	8.50 mm
Height H	33.00 mm
Outside diameter D	16.50 mm
d2	4.2 mm
Thread G1	G1/8"-F
Thread G2	G1/4"-F

Art.-Nr.: 10.02.01.01729

**Technical data**

Attribute	Value
Nozzle diameter	0.6 mm
Recommended hose internal diameter compressed air	4.0 mm
Recommended hose internal diameter vacuum	6.0 mm
Degree of evacuation	70.0 %
Sound pressure level suction	56.0 dB(A)
Sound pressure level free	67.0 dB(A)
Weight	90.9 g
Air consumption suction	0.660 cfm
Suction rate (max.)	1.500 cfm
Optimal operating pressure	4.00 bar
Number of stages	2
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	0 ... 60 °C
Optimal pressure	58.0 psi
Product family	SBP-HV-HF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01729**Ordering Data Accessories 10.02.01.01729**

Typ		Item number
Mounting set	SET SFE 13	10.02.01.01579
Mounting bracket	BEF-WIN 36x40x27 5 SFE-13	10.08.03.00314
Quick release valve	SEV G1/8-IG G1/4-AG	10.02.01.01471

**Ordering Data Spare Parts 10.02.01.01729**

Typ		Item number
Schmalz Fixation Element	SFE 13 AL	10.02.01.01419
Schmalz Holder Cap	SHC 2 13	10.02.01.01496
Silencer (round)	SD 16.5x51.5 SHC 13	10.02.01.01498
Ejector module	SEP HF 2 06 13	10.02.01.01343

