




SCPi 15 NC RD M12-5

Compact ejector SCPi / SMPi is delivered as a ready-to-connect product (without connection cable).

Available accessories: connection cable, connection distributor, compressed air connection plate, ejector blanking plate, quick change Connection (Adapter Quick Change), ejector tester

Technical data

Attribute	Value
Nozzle diameter	1.5 mm
Electrical connection	Male connect M12, 5 pol
Protection type IP	IP 65
Max. vacuum	-850 mbar
Air consumption suction	115.0 l/min
Suction rate (max.)	75.0 l/min
Pressure range (operating pressure) [bar]	4.0 ... 7.0 bar
Control valve	Normally closed
Functionality of the ejector	Digital air-saving function



Design data SCPi 15 NC RD M12-5

Design data

Attribute	Value
Length L1	129.70 mm
Length L2	112.50 mm
Length L	118.50 mm
Width B	22.00 mm
Height H1	131.50 mm
Height H2	71.50 mm
Height H	181.50 mm
Internal diameter d	6.60 mm
Thread G1	G1/4"-F
Thread G2	G3/8"-F

Art.-Nr.: 10.02.02.03346

**Technical data**

Attribute	Value
Nozzle diameter	1.5 mm
Recommended hose internal diameter compressed air	6.0 mm
Recommended hose internal diameter vacuum	6.0 mm
Degree of evacuation	85.0 %
Sound pressure level free	75.0 dB(A)
Weight	0.560 kg
Max. air consumption blow-off	200.0 l/min
Air consumption suction	4.061 cfm
Suction rate (max.)	2.648 cfm
Pressure range (operating pressure) [bar]	58.0 ... 101.5
Operating temperature	0 ... 50 °C
Max. vacuum	-25.100 inHg
Product family	SCPi
Control valve	Normally closed

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m




Art.-Nr.: 10.02.02.03346

**Performance data**

Achievable vacuum at various operating pressures



Evacuation time for various vacuum ranges [s/l]



Suction rate at various degrees of evacuation [l/min]

**Achievable vacuum at various operating pressures**

	2	3	4	5	6
SCPi / SMPi	350	610	800	890	850



Art.-Nr.: 10.02.02.03346

**Evacuation time for various vacuum ranges [s/l]**

	0	100	200	300	400	500	600	700	800
SCPi/SMPi 15	0.03	0.07	0.16	0.27	0.42	0.63	0.91	1.37	2.60
SCPi/SMPi 20	0.02	0.04	0.08	0.14	0.22	0.31	0.44	0.66	1.54
SCPi/SMPi 25	0.01	0.02	0.05	0.09	0.14	0.20	0.28	0.42	0.86

**Suction rate at various degrees of evacuation [l/min]**

	0	100	200	300	400	500	600	700	800
SCPi 15	75.0	65.4	55.2	46.3	38.3	31.2	23.9	13.5	3.4
SCPi 20	139.0	123.1	106.8	92.5	79.3	65.2	51.9	32.1	8.5
SCPi 25	195.0	176.8	153.6	133.6	112.0	89.3	67.4	39.7	11.7

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.02.03346**Ordering Data Accessories 10.02.02.03346**

Typ		Item number
Connection cable	ASK B-M12-5 5000 K-5P	21.04.05.00080
Distributor	ASV SM/CPi B-M12-5 3xS-M12-4	10.02.02.03372
Distributor	ASV SM/CPi B-M12-5 2xS-M12-4	10.02.02.03490
Compressed-air connection plate	GP 2 SMP 15..30/SCP 20..30	10.02.02.00917
Compressed-air connection plate	GP 3 SMP 15..25/SCP 20..25	10.02.02.00918
Compressed-air connection plate	GP 4 SMP 15..20/SCP 20	10.02.02.00919
Compressed-air connection plate	GP 5 SMP 15	10.02.02.00920
Compressed-air connection plate	GP 6 SMP 15	10.02.02.00921
Ejector blanking plate	EJEK-PL SMP(i)15..30/SCP(i)20..30	10.02.02.00728
Adapter Quick Change	ADP-Q 90.5x22x29.7 SMPi/SCPi	10.02.02.03463
Ejector tester	EJEK-TEST SMPi/SCPi	10.02.02.03588
Vacuum cup filter	VFT G1/4-IG 80	10.07.01.00119

**Ordering Data Spare Parts 10.02.02.03346**

Typ		Item number
Silencer (cube-shaped)	SD 111x21x45 SMPi/SCPi	10.02.02.03381



Compact ejector

SCPi 15 NC RD M12-5



Art.-Nr.: 10.02.02.03346



Ordering Data Wear Parts 10.02.02.03346

Typ		Item number
Set of parts subject to wear ejector	VST SMPI/SCPI	10.02.02.99965
Set of wearing parts ejector	VST SCPI-ERW	10.02.02.99963



WWW.SCHMALZ.COM/10.02.02.03346