

Art.-Nr.: 10.03.01.00147




EVE-TR 25 AC3 F

The vacuum pump EVE-TR comes ready to connect.

Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Attribute	Value
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	190 - 242 V / 342 - 440 V AC3
Voltage at 60 Hz	190 - 265 V / 342 - 500 V AC3
Weight	27.000 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	-850 mbar



Design data EVE-TR 25 AC3 F

Design data


Attribute	Value
Length L2	96.00 mm
Length L	505.00 mm
Width B2	40.00 mm
Width B	260.00 mm
Height H1	380.00 mm
Height H2	70.00 mm
Height H	290.00 mm
Internal diameter d	7.00 mm
Thread G2	G3/4"-F
Hole spacing Y1	208.0 mm

Art.-Nr.: 10.03.01.00147

**Technical data**

Attribute	Value
Protection type IP	IP 54
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	190 - 242 V / 342 - 440 V AC3
Voltage at 60 Hz	190 - 265 V / 342 - 500 V AC3
Weight	27.000 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Version	IE3:EU/CN/IND
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	200	400	600	800	850
EVE-TR 25 50 Hz	25	18.5	12.5	6.8	1.5	0.5
EVE-TR 25 60 Hz	30	23	16	8.7	2.2	0.7



Art.-Nr.: 10.03.01.00147

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00147**Ordering Data Accessories 10.03.01.00147**

Typ		Item number
Vacuum limiter valve	VBV -950...0 G1-AG EVE 10-40	10.03.01.00136
Motor-protection switch	MSS-K 1.6-2.5A	10.04.04.00119
Silencer box	SBB-EVE-24V-DC-ST-VZ-LUE	10.04.04.00367

**Ordering Data Spare Parts 10.03.01.00147**

Typ		Item number
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017
Filter insert (round)	FILT-EINS 64x71 PAP EVE-TR-25-40-50	10.03.01.00029

**Ordering Data Wear Parts 10.03.01.00147**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-25	10.03.01.00134