

Art.-Nr.: 10.03.01.00212



EVE-TR-X 16 AC3 VBV


Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

Technical data

Attribute	Value
Rated power at 50 Hz	0.55 kW
Rated power at 60 Hz	0.70 kW
Voltage at 50 Hz	175 - 260 / 300 - 450 V AC3
Voltage at 60 Hz	202-300/350-520V AC3
Weight	22.500 kg
Suction rate (50 Hz)	16.000 m ³ /h
Suction rate (60 Hz)	19.000 m ³ /h
Sound pressure level at 50 Hz	61.0 dB(A)
Vacuum (50 Hz)	-850 mbar
Voltage 60 Hz	202-300



Design data EVE-TR-X 16 AC3 VBV

Design data

Attribute	Value
Length L2	73.00 mm
Length L	452.00 mm
Width B2	66.00 mm
Width B	231.00 mm
Height H	205.00 mm
Internal diameter d	7.00 mm
Hole spacing Y1	125.0 mm
Hole spacing X1	202.0 mm
Thread G3	G1/2"-F

Art.-Nr.: 10.03.01.00212

**Technical data**

Attribute	Value
Protection type IP	IP 54
Rated power at 50 Hz	0.55 kW
Rated power at 60 Hz	0.70 kW
Voltage at 50 Hz	175 - 260 / 300 - 450 V AC3
Voltage at 60 Hz	202-300/350-520V AC3
Weight	22.500 kg
Suction rate (50 Hz)	16.000 m ³ /h
Suction rate (60 Hz)	19.000 m ³ /h
Sound pressure level at 50 Hz	61.0 dB(A)
Product family	EVE-TR-X
Supply voltage	AC3
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00212**Ordering Data Accessories 10.03.01.00212**

Typ		Item number
Vacuum limiter valve	VBV -950...0 G1-AG EVE 10-40	10.03.01.00136
Vacuum reservoir	VOL 15	10.03.03.00113

**Ordering Data Wear Parts 10.03.01.00212**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-X-16	10.03.01.00224

