



EVE-TR-X 40 AC3 VBV


Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

Technical data

Attribute	Value
Rated power at 50 Hz	1.25 kW
Rated power at 60 Hz	1.50 kW
Voltage at 50 Hz	190 - 255 V / 330 - 440 V AC3
Voltage at 60 Hz	190 - 290 V / 330 - 500 V AC3
Weight	38.500 kg
Suction rate (50 Hz)	40.000 m ³ /h
Suction rate (60 Hz)	48.000 m ³ /h
Sound pressure level at 50 Hz	67.0 dB(A)
Vacuum (50 Hz)	-900 mbar
Vacuum (60 Hz)	-900 mbar



Design data EVE-TR-X 40 AC3 VBV

Design data

Attribute	Value
Length L1	572.00 mm
Length L2	131.00 mm
Length L	532.00 mm
Width B2	51.00 mm
Width B	280.00 mm
Height H	290.00 mm
Internal diameter d	7.00 mm
Hole spacing Y1	190.0 mm
Hole spacing X1	220.0 mm
Thread G3	G3/4"-F

Art.-Nr.: 10.03.01.00218

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	1.25 kW
Rated power at 60 Hz	1.50 kW
Voltage at 50 Hz	190 - 255 V / 330 - 440 V AC3
Voltage at 60 Hz	190 - 290 V / 330 - 500 V AC3
Weight	38.500 kg
Suction rate (50 Hz)	40.000 m ³ /h
Suction rate (60 Hz)	48.000 m ³ /h
Sound pressure level at 50 Hz	67.0 dB(A)
Product family	EVE-TR-X
Supply voltage	AC3

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00218**Ordering Data Accessories 10.03.01.00218**

Typ		Item number
Vacuum limiter valve	VBV -950...0 G1-AG EVE 10-40	10.03.01.00136
Vacuum reservoir	VOL 50	10.03.03.00118
Silencer box	SBB-EVE-24V-DC-ST-VZ-LUE	10.04.04.00367

**Ordering Data Wear Parts 10.03.01.00218**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-X-40	10.03.01.00226

