

Art.-Nr.: 10.03.01.00352



EVE-TR-X 40 AC3 IE3-TYP2 VBV


Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

### Technical data

Rated power at 60 Hz	1.30 kW
Voltage at 60 Hz	YY230 / Y460 V $\pm 10$ %
Weight	41.000 kg
Suction rate (60 Hz)	48.000 m <sup>3</sup> /h
Voltage at 60 Hz optimal	D208 V $\pm 10$ % (without IE3)
Version	IE3:US/CAN
Vacuum (60 Hz)	-900 mbar
Voltage 60 Hz	S067
Approval	UL/CSA
Current type	Three phase A.C.
with	Vacuum-limiter valve



Design data EVE-TR-X 40 AC3 IE3-TYP2 VBV

### Design data

Length L2	131.00 mm
Length L	572.00 mm
Width B2	50.00 mm
Width B	270.00 mm
Height H	293.00 mm
Internal diameter d	7.00 mm
Hole spacing Y1	190.0 mm
Hole spacing X1	220.0 mm
Thread G3	G3/4"-F

Art.-Nr.: 10.03.01.00352

**Technical data**

Protection type IP	IP 55
Rated power at 60 Hz	1.30 kW
Voltage at 60 Hz	YY230 / Y460 V ±10 %
Weight	41.000 kg
Suction rate (60 Hz)	48.000 m <sup>3</sup> /h
Product family	EVE-TR-X
Supply voltage	AC3

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Ordering Data Accessories 10.03.01.00352**

Typ		Item number
Vacuum reservoir	VOL 50	10.03.03.00118
Silencer box	SBB-EVE-24V-DC-ST-VZ-LUE	10.04.04.00367

**Ordering Data Spare Parts 10.03.01.00352**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-X-40	10.03.01.00226
Filter insert (round)	FILT-EINS EVE-TR-X-25/40	10.03.01.00230

**Ordering Data Wear Parts 10.03.01.00352**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-X-40	10.03.01.00226

