

Art.-Nr.: 10.03.02.00020



EVE-OG 25 AC3 F


Vacuum pump EVE-OG is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert), replacement oil, maintenance kit (set of parts subject to wear pump)

Available accessories: motor-protection switch, filter resistance gauge (pressure manometer)

Technical data

Attribute	Value
Rated power at 50 Hz	0.75 kW
Weight	34.500 kg
Suction rate (50 Hz)	25.000 m ³ /h
Current type	Three phase A.C.
with	Filter



Design data EVE-OG 25 AC3 F


Design data

Attribute	Value
Length L2	131.00 mm
Length L	568.00 mm
Width B2	17.00 mm
Width B	284.00 mm
Height H1	380.00 mm
Height H2	75.00 mm
Height H	260.00 mm
Thread G2	G3/4"-F
Hole spacing Y1	238.0 mm
Hole spacing Y2	171.0 mm

Art.-Nr.: 10.03.02.00020

**Technical data**

Attribute	Value
Rated power at 50 Hz	0.75 kW
Weight	34.500 kg
Suction rate (50 Hz)	25.000 m ³ /h
Product family	EVE-OG
Supply voltage	AC3

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	200	400	600	800	1000
EVE-OG 25 50 Hz	25	20	14.9	9.8	4.7	-
EVE-OG 25 60 Hz	30	23.5	17.5	11.5	5.5	-

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00020WWW.SCHMALZ.COM/10.03.02.00020

Vacuum pump

EVE-OG 25 AC3 F



Art.-Nr.: 10.03.02.00020



Ordering Data Accessories 10.03.02.00020

Typ		Item number
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Set of parts subject to wear pump	VST EVE-OG-25-40	10.03.02.00060
Accessories	ZUB EVE-OG Ölablass-Kit	22.09.03.00038



WWW.SCHMALZ.COM/10.03.02.00020