

Art.-Nr.: 10.03.01.00216



EVE-TR-X 25 AC3 F-VB


Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

Technical data

Attribute	Value
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	190 - 242 V / 342 - 440 V AC3
Voltage at 60 Hz	190 - 265 V / 342 - 500 V AC3
Weight	26.500 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Vacuum (50 Hz)	-900 mbar
Vacuum (60 Hz)	-900 mbar



Design data EVE-TR-X 25 AC3 F-VB

Design data

Attribute	Value
Length L2	96.00 mm
Length L	505.00 mm
Width B2	40.00 mm
Width B	260.00 mm
Height H1	380.00 mm
Height H2	70.00 mm
Height H	290.00 mm
Internal diameter d	7.00 mm
Thread G2	G3/4"-F
Hole spacing Y1	190.0 mm

Art.-Nr.: 10.03.01.00216

**Technical data**

Attribute	Value
Protection type IP	IP 54
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	190 - 242 V / 342 - 440 V AC3
Voltage at 60 Hz	190 - 265 V / 342 - 500 V AC3
Weight	26.500 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Product family	EVE-TR-X
Supply voltage	AC3

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00216**Ordering Data Accessories 10.03.01.00216**

Typ	Item number
Silencer box	SBB-EVE-24V-DC-ST-VZ-LUE 10.04.04.00367

**Ordering Data Spare Parts 10.03.01.00216**

Typ	Item number
Set of parts subject to wear pump	VST EVE-TR-X-25 10.03.01.00225
Filter insert (round)	FILT-EINS EVE-TR-X-25/40 10.03.01.00230

