


Art.-Nr.: 10.03.01.00332

**Technical data**


Attribute	Value
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	108.000 kg
Suction rate (60 Hz)	112.000 m ³ /h
Voltage at 60 Hz optimal	D208 V ± 10 % (without IE3)
Version	IE3:US/CAN
Vacuum (60 Hz)	-900 mbar
Voltage 60 Hz	S067
Approval	UL/CSA
Current type	Three phase A.C.

EVE-TR-X 100 AC3 IE3-TYP2 VBV

Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

**Design data**

Attribute	Value
Length L2	140.00 mm
Length L	851.00 mm
Width B2	107.50 mm
Width B	470.00 mm
Height H	336.00 mm
Internal diameter d	12.00 mm
Hole spacing Y1	245.0 mm
Hole spacing Y2	122.5 mm
Hole spacing X1	398.0 mm
Thread G3	G1-1/2"-F

Design data EVE-TR-X 100 AC3 IE3-TYP2 VBV



Art.-Nr.: 10.03.01.00332

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V $\pm 10\%$
Weight	108.000 kg
Suction rate (60 Hz)	112.000 m ³ /h
Product family	EVE-TR-X
Supply voltage	AC3

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00332**Ordering Data Accessories 10.03.01.00332**

Typ	Item number
Vacuum reservoir	VOL 100 10.03.03.00123

**Ordering Data Spare Parts 10.03.01.00332**

Typ	Item number
Filter insert (round)	FILT-EINS EVE-TR-X-80/100/140 10.03.01.00231
Filter insert (round)	FILT-EINS EVE-TR-X-80 10.03.01.00232

**Ordering Data Wear Parts 10.03.01.00332**

Typ	Item number
Set of parts subject to wear pump	VST EVE-TR-X-100 10.03.01.00233

