

Compact Pump

GCPI 50 5xM12-5



Art.-Nr.: 10.03.01.00648



Technical data

Attribute	Value
Electrical connection	5xConnect M12, 5x5 pol
Protection type IP	IP 54
Max. vacuum	800 mbar
Weight	3,220.0 g
Suction rate (max.)	46.0 l/min
Operating temperature	0 ... 45 °C
Voltage	24V - DC
Size	50
Sound pressure level (max.)	67.0 dB(A)

GCPI 50 5xM12-5


The Electric Compact Pump GCPI is delivered as a ready-to-connect product.

Available spare parts: silencer, filter screen

Available accessories: connection cable

Design data

Attribute	Value
Length L1	220.00 mm
Length L	190.00 mm
Width B2	47.00 mm
Width B	236.00 mm
Height H	102.00 mm
Internal diameter d	6.60 mm
Thread G1	G1/4"-F
Thread G2	M12x1-M
Hole spacing Y1	166.0 mm
Hole spacing X1	204.0 mm



Design data GCPI 50 5xM12-5



WWW.SCHMALZ.COM/10.03.01.00648

Art.-Nr.: 10.03.01.00648

**Technical data**

Attribute	Value
Electrical connection	5xConnect M12, 5x5 pol
Weight	3,220.0 g
Voltage DC	24 V - DC
Suction rate (max.)	46.0 l/min
Operating temperature	0 ... 45 °C

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00648**Ordering Data Accessories 10.03.01.00648**

Typ		Item number
Power cable	P-LEIT-LK B-M12-5 5m OK	21.04.05.00352
Connection cable	ASK B-M12-5 5000 K-5P	21.04.05.00080
Connection cable	AK-SB-M12-G 5m A 5P	21.04.05.00931
Power supply unit	NETZ 96VA 24V-DC 100-240-AC	21.07.01.00205
Vacuum cup filter	VFT G1/4-IG 80	10.07.01.00119
Accessories	ZUB GCPi GUMMI-PUFF	10.03.01.00809

**Ordering Data Spare Parts 10.03.01.00648**

Typ		Item number
Sieve, round	SIEB 14x2 A2 0.415/0.22	10.02.02.03377
Silencer (round)	SD G3/8-AG 20x56 SEG	10.02.01.00905
Housing (complex shape)	GEH 94x31x46.15 GCPi	10.03.01.00888

