

Art.-Nr.: 10.03.02.00083



EVE-OG 16 AC3 F


Vacuum pump EVE-OG is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert), replacement oil, maintenance kit (set of parts subject to wear pump)

Available accessories: motor-protection switch, filter resistance gauge (pressure manometer)

Technical data

Attribute	Value
Rated power at 50 Hz	0.50 kW
Voltage at 50 Hz	230 / 400 V AC
Voltage at 60 Hz	230 / 400 V AC
Weight	19.600 kg
Suction rate (50 Hz)	16.000 m ³ /h
Suction rate (60 Hz)	19.000 m ³ /h
Sound pressure level at 50 Hz	44.0 dB(A)
Current type	Three phase A.C.
with	Filter



Design data EVE-OG 16 AC3 F


Design data

Attribute	Value
Length L2	63.00 mm
Length L	435.00 mm
Width B2	26.00 mm
Width B	215.00 mm
Height H1	305.00 mm
Height H2	70.00 mm
Height H	215.50 mm
Thread G2	G3/4"-F
Hole spacing Y1	111.0 mm
Hole spacing Y2	107.0 mm

Art.-Nr.: 10.03.02.00083

**Technical data**

Attribute	Value
Protection type IP	IP 55
Max. vacuum	-28.939 inHg
Rated power at 50 Hz	0.50 kW
Voltage at 50 Hz	230 / 400 V AC
Weight	19.600 kg
Suction rate (50 Hz)	16.000 m ³ /h
Sound pressure level at 50 Hz	44.0 dB(A)
Product family	EVE-OG
Supply voltage	AC3

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	200	400	600	800	1000
EVE-OG 16 50 Hz	16	12.9	9.3	6.1	3	-
EVE-OG 16 60 Hz	19	15.2	11.2	7.2	3.3	-

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00083WWW.SCHMALZ.COM/10.03.02.00083

Vacuum pump

EVE-OG 16 AC3 F



Art.-Nr.: 10.03.02.00083



Ordering Data Accessories 10.03.02.00083

Typ		Item number
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Accessories	ZUB EVE-OG Ölablass-Kit	22.09.03.00038



WWW.SCHMALZ.COM/10.03.02.00083