

Art.-Nr.: 10.03.02.00032



EVE-OG 63 AC3 F


Vacuum pump EVE-OG is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert), replacement oil, maintenance kit (set of parts subject to wear pump)

Available accessories: motor-protection switch, filter resistance gauge (pressure manometer)

Technical data

Attribute	Value
Rated power at 50 Hz	1.50 kW
Voltage at 50 Hz	200 - 240 V or 345 - 420 V
Weight	52.000 kg
Suction rate (50 Hz)	63.000 m ³ /h
Sound pressure level at 50 Hz	65.0 dB(A)
Current type	Three phase A.C.
with	Filter



Design data EVE-OG 63 AC3 F


Design data

Attribute	Value
Length L2	137.00 mm
Length L	614.00 mm
Width B2	15.00 mm
Width B	406.00 mm
Height H1	417.00 mm
Height H2	75.00 mm
Height H	280.00 mm
Thread G2	G1-1/4"-F
Hole spacing Y1	277.0 mm
Hole spacing X1	199.0 mm

Art.-Nr.: 10.03.02.00032

**Technical data**

Attribute	Value
Protection type IP	IP 54
Max. vacuum	-28.939 inHg
Rated power at 50 Hz	1.50 kW
Voltage at 50 Hz	200 - 240 V or 345 - 420 V
Weight	52.000 kg
Suction rate (50 Hz)	63.000 m ³ /h
Sound pressure level at 50 Hz	65.0 dB(A)
Product family	EVE-OG
Supply voltage	AC3

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	200	400	600	800	1000
EVE-OG 63 50 Hz	63	50	36.5	24	11	-
EVE-OG 63 60 Hz	75	60	45	28	13.5	-

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00032WWW.SCHMALZ.COM/10.03.02.00032

Art.-Nr.: 10.03.02.00032

**Ordering Data Accessories 10.03.02.00032**

Typ		Item number
Motor-protection switch	MSS-K 4-6.3A	10.04.04.00121
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Accessories	ZUB EVE-OG Ölablass-Kit	22.09.03.00038

**Ordering Data Spare Parts 10.03.02.00032**

Typ		Item number
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018

**Ordering Data Wear Parts 10.03.02.00032**

Typ		Item number
Set of parts subject to wear pump	VST EVE-OG-63-100	10.03.02.00055