


Art.-Nr.: 10.03.02.00094



EVE-OG 100 AC3 AQUA IE3

Technical data

Attribute	Value
Rated power at 50 Hz	2.70 kW
Rated power at 60 Hz	3.40 kW
Voltage at 50 Hz	190-208 V / 380 - 415 V AC3
Voltage at 60 Hz	220 - 230 V / 440 - 480 V AC3
Suction rate (50 Hz)	100.000 m ³ /h
Length L	700.00 mm
Current type	Three phase A.C.

Design data

Attribute	Value
Length L	700.00 mm
Width B	406.00 mm
Height H	290.00 mm
Thread G3	G1-1/4"-F
Thread G5	M8-F

Design data EVE-OG 100 AC3 AQUA IE3



Art.-Nr.: 10.03.02.00094

**Technical data**

Attribute	Value
Protection type IP	IP 55
Max. vacuum	-980 mbar
Rated power at 50 Hz	2.70 kW
Rated power at 60 Hz	3.40 kW
Voltage 50 Hz	S052
Voltage at 50 Hz	190-208 V / 380 - 415 V AC3
Voltage at 60 Hz	220 - 230 V / 440 - 480 V AC3
Suction rate (50 Hz)	100.000 m ³ /h
Suction rate -800	100.0 m ³ /h
Voltage 60 Hz	S053
Current type	Three phase A.C.
Type	AQUA

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00094