



EVE-OG 10 AC3

**Technical data**

| Attribute                     | Value                    |
|-------------------------------|--------------------------|
| Rated power at 50 Hz          | 0.37 kW                  |
| Weight                        | 7.700 kg                 |
| Suction rate (50 Hz)          | 10.500 m <sup>3</sup> /h |
| Sound pressure level at 50 Hz | 58.5 dB(A)               |
| Height H                      | 177.00 mm                |
| Current type                  | Three phase A.C.         |

Design data EVE-OG 10 AC3

**Design data**

| Attribute | Value     |
|-----------|-----------|
| Length L  | 291.00 mm |
| Width B   | 222.00 mm |
| Height H  | 177.00 mm |

**Technical data**

| Attribute   | Value     |
|-------------|-----------|
| Max. vacuum | -998 mbar |

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.03.02.00111](http://www.schmalz.com/10.03.02.00111)